

# Ax60



## CO2 Safety Monitor



### KEY FEATURES

**Multi-point CO2 detector**

**Approved by leading global fast food outlet**

**Central unit can be checked away from the danger zone**

**5-year sensor and electronics warranty**

**Low maintenance**

**TWA monitoring**

### APPLICATIONS

- Pub cellars
- Breweries
- Wineries
- Fast food restaurants
- Sports stadiums
- Swimming pools
- Leisure centres
- Kitchens
- Cafes

### Why?

Standards around the world, including EH40, OSHA and TUV, mandate that employees and members of the public are not exposed to potentially dangerous levels of CO2 as it's a highly toxic gas in relatively small quantities.

### What?

The Ax60 is a wall mountable carbon dioxide (CO2) detector. Designed specifically for the hospitality industry, the Ax60 allows multiple placement of Alarm and Sensor units which are connected to a Central Display. Each Alarm unit not only has an audible sounder but also utilises a high-intensity LED strobe light – perfect for warning of danger in noisy environments.

### Where?



The Central Display is wall mounted in a convenient location such as an office. This monitors Sensor units that are mounted at low level in areas highlighted as a risk. Each Sensor is connected to one or more Alarm units to ensure warning of potential dangers is highlighted to everyone.



**THE EXPERTS IN BEVERAGE  
& HOSPITALITY GAS SAFETY**

**ANALOX**  
Sensor Technology

## SPECIFICATIONS



Analog has a policy of continuous improvement and we reserve the right to upgrade or change specifications without prior notice.  
**Full technical specifications are available upon request and can be found in the User Manual.**  
 If you require a datasheet in another language please contact us.

Unless your local regulations state otherwise the Ax60 will NEVER need calibrating.

### System

**Warranty:** 5 years

**Warm-up time:** 40 seconds

**Operating temperature range:** -5 °C to +50 °C,  
 +23 °F to +122 °F

**Approvals:** CE, EN50270, IEC 61010 (UL),  
 DIN 6653 (TUV)

### Central Display

**Display:** LCD dot matrix (backlit)

**Relays:** 2 off, default normally open. Rating 1  
 A/30 V AC/DC

**IP Rating:** IP54

### CO2 Alarm

**Strobe:** white LED strobe > 100 cd  
 (optional blue or red filter)

**Sounder:** min 80 dBA @3 m (9.8 feet)

**IP Rating:** IP55

### CO2 Sensor

**Gas detected:** carbon dioxide


**Measurement technique:** infrared

**Range:** 0.1% to 5%

**Default alarm setpoints:** 0.5% (8 hour TWA),  
 1.5%, 3.0%

**IP Rating:** IP55

**Alarm set points can be changed by the user.**



[www.analoxsensortechnology.com](http://www.analoxsensortechnology.com)



UK: +44 (0) 1642 711400

US: +1 (714) 891 4478



info@analox.biz

**ANALOX**  
 Sensor Technology