

# PSA Nitrogen Generator

# N2-AS-N



AirSep Alpha Series Nitrogen Generators produce from 450 to 44,671 cubic feet of nitrogen per hour at 99.5% nitrogen concentration. When electricity and an adequate source of compressed air is supplied, these dependable machines can provide nitrogen for practically any application and at concentrations up to 99.999% (10 PPM O<sub>2</sub>).

## Features

- Produces nitrogen from an independent compressed air source
- Microprocessor controlled
- Low operating cost with energy efficient programming control options
- Automatic and unattended operation
- Easy to install and maintain
- NEMA 4X Touchscreen control panel with integrated nitrogen concentration monitor

## Typical Applications

### Manufacturing

- Cutting/Brazing/Soldering
- Heat Treatment
- High Pressure Plastic Injection Molding

### Oil & Gas/Power Generation

- Onshore/Offshore Exploration
- Mechanical Gas Seal Inerting
- Enhanced Oil Recovery (EOR)

### Food & Beverage

- Modified Atmosphere Packaging (MAP)
- Nitrogen CO<sub>2</sub> Gas Mix Beer Drafting
- Controlled Atmosphere(CA)/Fruit Storage
- Wine Bottle Capping

### Automotive

- Tire Inflation

### Mining


- Control of Lower Explosive Limits (LEL)

## Specifications

Product Flow	10,012 SCFH (263 Nm <sup>3</sup> /hr) <sup>1</sup>
Product Pressure	85 – 90 psig (586 – 621 kPa or 5.8 – 6.2 barg) <sup>1</sup>
Product Concentration	99.5%
Product Dew Point	-100°F (-73°C)
Dimensions (W x D x H) (Nominal)	84 x 48 x 110 in (213 x 122 x 279 cm)
Weight	4,950 lb (2,245 kg)
Physical Connections	
Compressed Air Inlet	2" FNPT
Product Gas Outlet	1½" FNPT
Ambient Operating Conditions	Locate the oxygen generator in a well-ventilated area that is protected from weather elements and remains between 40°F (4°C) and 104°F (40°C)
Feed Air Requirements	Flow Rate: 476 SCFM (12.51 Nm <sup>3</sup> /min) <sup>1</sup> Clean and Dry "Plant Air" (Class 5.6.4 per ISO 8573.1) Pressure: 109 psig (752 kPa) minimum Temperature: 109°F (43°C) maximum Dew Point: 40°F (4.4°C) maximum
Control Power Requirements (Single Phase)	120 V ~ ±10%, 50/60 Hz, 3.0 A or 220 V ~ ±10%, 50/60 Hz, 1.0 A
Certifications and Approvals	ASME, CSA, UL
<b>1,060 Gallon Nitrogen Receiver</b>	
Dimensions (Dia. x H)	56 x 152 in (142 x 386 cm)
Weight	2,000 lb (907 kg)

<sup>1</sup> SCF (Standard cubic foot) gas measured at 1 atmosphere and 70°F / Nm<sup>3</sup> (Normal cubic meter) gas measured at 1 atmosphere and 0°C

<sup>2</sup> Hose and applicable adapters included with optional Factory-supplied accessory kits.



Note: All dimensions are nominal.

### Model N2-AS-N Nitrogen Generator Feed Air Requirement\*

Nitrogen Concentration%	Feed Air Usage**	N2-AS-N
99.99		4,780
99.95		6,354
99.9		7,228
99.5	476 SCFM	10,012
99		10,518
98		13,873
97		15,971
96		18,069
95		18,972

\*\*Time weighted average. Contact Factory for air compressor sizing assistance.  
\* SCF (Standard cubic foot) gas measured at 1 atmosphere and 70°F

### Ordering Information

Model	Part Number	Description
N2-AS-N	NGAS092-7	With HMI NEMA 4X Touchscreen and nitrogen concentration monitor, 120 V ~ ±10%, 50/60 Hz <sup>1</sup>
	NGAS092-8	With HMI NEMA 4X Touchscreen and nitrogen concentration monitor, 220 V ~ ±10%, 50/60 Hz <sup>1</sup>
Required Accessories	TA082-1	1,060 Gallon Oxygen Receiver
Optional Accessories	KI600-X	Accessory Kit (flow control manifold)
Interconnecting hoses available. Contact Factory for details.		
Shipping Information		N2-AS-N
		1,060 Gallon Oxygen Receiver
Class	92.5	70
Commodity Classification Number	8421.39.8040	7311.00.0000
Dimensions (W x D x H)	88 x 114 x 55 in (224 x 290 x 140 cm) with Filter and Pallet	52 x 156 x 60 in (132 x 396 x 152 cm)
Gross Weight	5,430 lb (2,463 kg) with Filter and Pallet	2,200 lb (998 kg)

### Warranty: 1 Year Parts and Factory Labor\*\*\*

\*\*\* An unprotected or inadequately ventilated environment, or improper control power may cause damage to the nitrogen generator not covered under warranty.

<sup>1</sup> Specify nitrogen flow and pressure at time of order.

All performance ratings based on an ambient temperature up to 100°F (38°C), up to 1,000 feet elevation, and 80% relative humidity.



© 2018 AirSep Corporation. All Rights Reserved.  
AirSep reserves the right to discontinue its products, or change the prices, materials, equipment, quality, descriptions, specifications and/or processes to its products at any time without prior notice and with no further obligation or consequence. Any rights expressly stated herein are reserved by us, as applicable.



260 Creekside Drive  
Buffalo, NY 14228-2075 U.S.A.  
Tel: (716) 691-0202 ■ Fax: (716) 691-1255  
www.airsepcpd.com ■ info@airsep.com  
ML-IND0044 A