



The Better Standard in Liquid Level Gauges



New & Improved Roto-Tel:

- Accuracy $\pm 5\%$
- Service: LIN, LAR, LOX, CO₂, N₂O
- Upgrades available for any Chart tank
- Standard on all factory liquid cylinders
- All mechanical float style gauge / no batteries required

Roto-Tel – The new liquid level gauge for all your cryogenic applications.

www.chartparts.com


1-800-400-4683



Innovation. Experience. Performance.®

C-Stic

The Best Option in Liquid Level Gauges



New Technology C-Stic:

- Capacitance level gauge technology
- Reliable digital level display reads % full
- Accuracy $\pm 1\%$
- Service: LIN, LAR, LOX, CO_2 , N_2O
- Retrofits to any liquid cylinder
- Factory upgrade to any new liquid cylinder
- DataOnline ready units available / supports other telemetry providers

C-Stic – If your application requires greater accuracy in your liquid level gauge, we have the technology.