


INSTALLATION MANUAL



Adjustable Pitch Fan Assembly 34' through 40' Diameter

Hudson Tuf-Lite II® fan blades

Hudson Tuf-Lite II® (white, prev. blue**) fan blades are made from fiberglass reinforced vinyl-ester resin having a very high strength-to-weight ratio and superior ultra-violet and corrosion resistance. An elastomeric blade/holder joint cover (not shown) prevents moisture from entering the blade (shown above).

The individually balanced blades can be replaced independently - matched sets are not required.

RECOMMENDED TOOLS

- Long T-Handle Allen Wrench Set (3/16" to 3/8")
- Medium Size Flat Head Screw Driver
- Brass Ball Peen Hammer
- Flat Bastard File
- 240 Grit Sand Paper
- Anti-Seize Lubricant
- WD-40
- 12" Crescent Wrench
- Shop Towels
- Exact-A-Pitch® Digital Protractor (P/N 62375)
- 25 ft. Measuring Tape
- Pencil or Marker
- Open/Box End Wrench Set (1/2" - 1-1/2")
- Socket Set for 1/2" Drive (1/2" - 1-1/2")
- Torque Wrench(s) Rated for 0-250 ft-lb.

INSTALLATION PROCEDURES

ASSEMBLY WITH BUSHING

Clean all mating surfaces between hub, bushing and shaft. If there is no shoulder on shaft to prevent bushing from sliding down shaft, slide spacer/sleeve (not provided) on shaft before bushing. Slide bushing and key onto shaft until flush with end of shaft. Lock W-2 bushing on shaft by tightening set screw in flange with 1/4" Allen Wrench. (Note: set screw is not present on all bushings) Line up key and set hub on bushing. Engage the four (4) 3/4" cap screws in flange of bushing into hub spool. Using a torque wrench with a 1-1/8" socket, tighten evenly to recommended standard of 250 ft-lb (dry).

ASSEMBLY WITH STRAIGHT SHAFT (NO BUSHING)

Clean all mating surfaces between the hub and the shaft. If there is no shoulder on shaft to prevent hub from sliding down shaft, slide spacer/sleeve (not provided) on shaft before hub or use a thrust retainer (optional equipment) on top of hub. Install key in shaft. Line up key and keyway and set hub on shaft. Tighten two (2) set screws in hub.

ASSEMBLY WITH TAPERED SHAFT (NO BUSHING REQUIRED)

Clean all mating surfaces between hub and shaft. Coat all mating surfaces with an anti-seize or lubricating compound.

Align keyways and install hub. Install retainer plate and cap screw(s) with lock washer(s). Shaft size determines what size cap screw is necessary. Using a torque wrench with a socket, evenly tighten cap screw to recommended standard per table below.

| Cap Screw Size | Socket Size | Torque Value (ft-lb) | |
|-------------------|----------------|-------------------------|-----|
| | | Lubricated | Dry |
| 5/8" NC | 15/16" | 100 | 110 |
| 3/4" NC | 1-1/8" | 125 | 130 |
| 1" NC | 1-1/2" | 150 | 160 |

NOTE: Retaining arrangement varies with gear shaft design.

ASSEMBLE BLADE CLAMP ON BLADE NECK

Remove blade clamp studs, lock washers, and blade clamp halves from hub. Assemble blade clamp halves over groove in blade neck, with thick leading edge to left and thin trailing edge to right as you stand at end of blade. Use a band clamp to hold the two blade clamp halves in position on the blade for installation in the hub body (See Figure 1).



Figure 1

INSTALL BLADE INTO HUB

Hoist the blade into position. (Blade and clamp halves weight about 300 lbs.) Slide blade clamp into blade arm plates and install four (4) blade studs, eight (8) lock washers and eight (8) nuts (See Figure 2). Tighten lightly.



Figure 2

SET PITCH AND TRACK

Use Hudson EXACT-A-PITCH® digital protractor (Shown in Figure 3) or a bubble protractor to set blade pitch. Mount protractor on a flat bar as a base and place it approximately 1" from tip of blade. Note pitch on protractor. Rotate fan 360°, noting high and low pitch readings. Locate place where pitch reading is a mid-point between high and low readings, and set pitch at that point.

Rotate blade in clamp until digital protractor shows specified pitch angle to within $\pm 0.2^\circ$. (*Fan pitch angle is shown on fan specification sheet for design duty.*)

After desired pitch angle is set, raise and lower end of fan blade and find midpoint of blade travel. Hold blade at the midpoint. Pull blade back so that it sits against blade clamp. Push blade to the right to remove all slack.

Use torque wrench to tighten clamp bolts to recommended standard of 280 ft-lb (lubricated) or 300 ft-lb (dry). Re-check pitch setting. Blade must be set within $\pm 0.2^\circ$ of desired pitch angle. Tighten clamp bolts evenly. **DO NOT OVERTORQUE CLAMP BOLTS.**



Figure 3

When bolts are tightened, hold a pencil against top end of blade and mark the level onto a fixed object, such as a pole or the fan ring.

Install remaining blades at same place as first blade, following procedures above. After tightening bolts, mark top end of each blade in same place first blade was marked. If marks differ by 1-1/2" or more, adjust blade.

CHECK TRACK

After fan is installed in fan ring, outline top end of each blade onto fan ring with a marker. The difference between levels of highest and lowest outlines should be within $\pm 2.5"$. Correct blade track by loosening clamp bolts and adjusting blade to match track of other blades. Re-tighten bolts and re-check track and pitch angle setting. Re-tighten blade clamp bolts to recommended standard of 280 ft-lb (lubricated) or 300 ft-lb (dry) torque (See Figure 4).



Figure 4

CHECK SWEEP

Measure the distance from trailing edge at blade tip of one blade to trailing edge at blade tip of the adjacent blade (See Figure 4a). This distance should be within 1-1/4" of each other for all successive blades. Correct blade sweep by loosening clamp bolts and adjusting blade to match sweep of other blades. Re-tighten bolts and re-check sweep and pitch angle setting. Re-tighten blade clamp bolts to recommended standard of 280 ft-lb (lubricated) or 300 ft-lb (dry) torque.




Figure 4a

SEAL DISC ASSEMBLY & INSTALLATION

Place seal-disc quarter section on hub, aligning the pear-shaped opening over one of the eyebolts (See Figure 5) and drop the seal-disc quarter section onto the nearest group of seal-disc bracket stud pairs. Remove adhesive backing on nitrile gasket section and apply gasket to seal-disc flange surface carefully such that holes in gasket lineup with the holes in the flange (See Figure 6). Repeat these operations with the next three seal-disc quarter sections, ensuring that seal-disc balance match marks are aligned.



Figure 5



Figure 6




Figure 7

Make final adjustments to the quarter sections such they mate properly with each other and all seal-disc bracket studs, install the fasteners loosely joining each seal-disc section using one flat washer against the fiberglass surface on each side, one 3/8" hex bolt, lock washer, and hex nut at each flange hole location (See Figure 7). Ensure final fit-up of the seal-disc sections, check flatness and alignment of pear-shape openings with the eyebolts, and snug all fasteners. Complete fasteners (Figure 8) at each bracket location (two per bracket) using a seal disc mounting pad (P/N A8105), a flat washer, lock washer, and hex nut according to Detail A on page 7. Snug these fasteners.



Figure 8



Figure 9

NOTE: The purpose of the seal disc is to prevent hot air from recirculating back down through the hub, increasing efficiency.



Figure 10

CHECK TIP CLEARANCE

Rotate fan in position inside fan ring or fan stack to check tip clearance. Check for spots where fan blade clearance is less than 3/4" or greater than 1-1/2" from fan ring (See Figure 10). If necessary adjust fan ring or fan stack by shimming to obtain proper clearance. Note that different cooling towers may have different ways to adjust the fan ring or fan stack.

OPERATING INSTRUCTIONS

Start fan and check rotation. Viewed from top, fan blades should rotate clockwise.

Hudson recommends to re-verify the blade clamp torque after the initial 10-15 minutes of cold operation (i.e., the fan doesn't need to be exposed to the working temperature of the process). This will ensure that the blades are settled within the clamps after the centrifugal forces have acted.

Check motor power consumption to be sure fan is pulling desired load. **CAUTION:** If positive pitch is set in summer to use all available motor amps (nameplate rating), motor could be overloaded in winter. Design pitch angles usually do not use all of the available motor horsepower. This ensures that the motors will not be overloaded at low winter temperatures.

For the fans that have remained idle (such as a shut-down or turn-around), it is highly recommended to re-verify the torque on the blade clamps before putting it back into operation.



Figure 11

PART LIST
HUDSON PRODUCTS CORPORATION
8000 Series Hub - Adjustable Pitch Fan Assembly 34' through 40' Diameter

| | | | | NO OF BLADES | | | | | | | | | |
|------|---|------|-----------------------------|-----------------------|---------------|---------------|---------------|---------------|---------------|---------------|---------------|---------------|--|
| ITEM | DESCRIPTION | TYPE | PART. NO | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | |
| | Up to 7.44 Diameter Shaft | W-2 | Hub Assy. No. Part. No. | 8906 D8116 | 8907 D8117 | 8908 D8118 | 8909 D8119 | 8910 D8120 | 8911 D8121 | 8912 D8122 | 8913 D8123 | 8914 D8124 | |
| 1 | Hub Plate (2 Per Hub) | W-2 | Part. No | D8126 | D8135 | D8128 | D8129 | D8130 | D8131 | D8132 | D8133 | D8134 | |
| ITEM | DESCRIPTION | TYPE | PART. NO | QUANTITY PER ASSEMBLY | | | | | | | | | |
| 2 | Hub Spool | W-2 | 65060 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | |
| 3 | Bushing | W-2 | Specify Bore | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | |
| 4 | Blade Clamp Half, Coal Tar Epoxy Coated Gray Cast Iron (Standard) Option 1: Powder Epoxy Coated Gray Cast Iron Option 2: Customer Specified Coating of Gray Cast Iron | | 65018 65018S (Varies) | 12 | 14 | 16 | 18 | 20 | 22 | 24 | 26 | 28 | |
| 5 | Blade Clamp Stud W/ 2 Nuts 1"-8 x 14-1/2" (Mech. Galv.) | | 70643 | 24 | 28 | 32 | 36 | 40 | 44 | 48 | 52 | 56 | |
| 6 | 1" Flat washer (Mech. Galv.) | | 57402 | 48 | 56 | 64 | 72 | 80 | 88 | 96 | 104 | 112 | |
| 7 | 1" Lock washer (Mech. Galv.) | | 73742 | 48 | 56 | 64 | 72 | 80 | 88 | 96 | 104 | 112 | |
| 8 | Hub Spool Cap Screw 3/4"-10 x 2-1/2" (316 SS) | | 57027 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | |
| 9 | 3/4" Flat washer (316 SS) | | 73720 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | |
| 10 | 3/4" Lock washer (316 SS) | | 73739 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | |
| 11 | Blade Arm, 44" Long | | 61650 | 12 | 14 | 16 | 18 | 20 | 22 | 24 | 26 | 28 | |
| 12 | Blade Arm Stiffener, 30-5/16" Long | | 61660 | 12 | 14 | 16 | 18 | 20 | 22 | 24 | 26 | 28 | |
| 13 | Bolt, HH, 1"-8 x 3" (Mech. Galv.) | | 59815 | 48 | 56 | 64 | 72 | 80 | 88 | 96 | 104 | 112 | |
| 14 | Bolt, HH, 1"-8 x 2-1/2" (Mech. Galv.) | | 69927 | 24 | 28 | 32 | 36 | 40 | 44 | 48 | 52 | 56 | |
| 15 | Nut, Heavy Hex, 1"-8NC (Mech. Galv.) | | 72120 | 72 | 84 | 96 | 108 | 120 | 132 | 144 | 156 | 168 | |
| 16 | 1" Flat washer (Mech. Galv.) | | 57402 | 144 | 168 | 192 | 216 | 240 | 264 | 288 | 312 | 336 | |
| 17 | 1" Lock washer (Mech. Galv.) | | 73742 | 72 | 84 | 96 | 108 | 120 | 132 | 144 | 156 | 168 | |
| 18 | Seal Disc Bracket Weldment | | B8136 | 8 | 8 | 8 | 8 | 8 | 8 | 8 | 8 | 8 | |
| 19 | A563 GR A HDG Hex Nut portion only, bolt is integral to seal disc bracket dwg 8136, P/N B8136 | | 15314 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | |
| 20 | Seal Disc Mounting Pad 1.50" OD X 0.375" ID X 0.25" THK | | A81 05 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | |
| 21 | Flat washer, 3/8" x 1-1/2" OD x 0.078 Thk (Mech Galv.) | | 73723 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | |
| 22 | Lock washer 3/8" (Mech. Galv.) | | 72974 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | |
| 23 | Cap Screw, HH, 3/8"-16NC x 3/4" (316 SS) | | 70033 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | |
| 24 | 3/8" Lock Washer (316 SS) | | 73722 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | 16 | |
| 25 | Eye Bolt W/ Nut 3/4"-10 x 2" (Mech. Galv.) | | 59547 | 4 | 4 | 4 | 4 | 4 | 4 | 4 | 4 | 4 | |
| 26 | 3/4" Flat Washer (Mech. Galv.) | | 16716 | 8 | 8 | 8 | 8 | 8 | 8 | 8 | 8 | 8 | |
| 27 | 3/4" Lock Washer (Mech. Galv.) | | 73738 | 4 | 4 | 4 | 4 | 4 | 4 | 4 | 4 | 4 | |
| 28 | 160" Diameter Seal Disc Kit * | | D8053 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | 1 | |
| 29 | Seal Disc Joint Gasket | | 73047 | 4 | 4 | 4 | 4 | 4 | 4 | 4 | 4 | 4 | |
| 30 | Seal Disc Cap Screw, HH, 3/8"-16NC x 2" (316 SS) | | 53622 | 24 | 24 | 24 | 24 | 24 | 24 | 24 | 24 | 24 | |
| 31 | Seal Disc Hex Nut, 3/8" (316 SS) | | 72050 | 24 | 24 | 24 | 24 | 24 | 24 | 24 | 24 | 24 | |
| 32 | Seal Disc Flat Washer 3/8" x 1" OD (316 SS) | | 73623 | 48 | 48 | 48 | 48 | 48 | 48 | 48 | 48 | 48 | |
| 33 | Seal Disc Lock Washer 3/8" (316 SS) | | 73722 | 24 | 24 | 24 | 24 | 24 | 24 | 24 | 24 | 24 | |
| 34 | Tuf-Lite II® Fan Blade (White) ** | | (Varies) | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | |

*Includes all hardware items 19 thru 22 and 29 thru 33 to assembly and mount.

**Blade color was blue prior to March 2006.

STANDARD MATERIALS & FINISHES

Blades: Fiberglass reinforced vinyl ester or epoxy

Hub Spool: Ductile Iron, Zinc Rich Coating

Plates: Coal Tar Epoxy coated steel

Bushing: Malleable Iron

Seal Disc: Fiberglass Reinforced Polyester

Blade Clamps:

Powder Epoxy Coated Die Cast Alum (Standard)

Powder Epoxy Coated Ductile Iron (Option 1)

Coal Tar Epoxy Coated Ductile Iron (Option 2)

Fasteners:

Steel, Mech. Galvanized & 316 SS Opt.

Complete Fan with 316 SS (Option 1)

Complete Fan with K500 Monel (Option 2)

WHEN ORDERING, SPECIFY FAN DIAMETER, TYPE & NUMBER OF BLADES & SHAFT DIAMETER

EXAMPLE:

APT

—

40H

—

8



6 1/2" BORE

Fan Model
Adjustable Pitch

Fan Diameter & Blade Type
(Specify "H" for Tuf-Lite II® Blades)

Number
of Blades

Shaft Diameter



PART LIST **HUDSON PRODUCTS CORPORATION** **8000 Series Hub - Adjustable Pitch Fan Assembly 34' through 40' Diameter**

HUDSON

Products Corporation

9660 Grunwald Rd.

Beasley, Texas 77417-8600

Phone: 281-396-8100

Fax: 281-396-8388

1-800-634-9160 (24 Hours)

[EMAIL: HUDSON@HUDSONPRODUCTS.COM](mailto:HUDSON@HUDSONPRODUCTS.COM)

<http://www.hudsonproducts.com>

Hudson, Auto-Variable, Combin-Aire, Exact-A-Pitch, Fin-Fan, Heatflo, Hy-Fin, Split-Flo, Solo Aire, Stac-Flo, Steamflo, Thermflo, Tuf-Edge, Tuf-Lite, Tuf-Lite II, and Tuf-Lite III are registered trademarks of Hudson Products Corporation.

©2012 Hudson Products Corp. All Rights Reserved.