



# Spencer Vortex<sup>®</sup> Regenerative Blowers


# Howden

## Dimensions

### Model VB037XP with special paint

Howden may make improvements and dimensional changes to equipment designs based on market trends and requirements.

Vortex<sup>®</sup> is a registered trademark of Howden.



Model No	Overall dimensions (inches)				TEFC Motor Specifications			Noise Level dB (A) at 1.5m (60Hz)	Weight (pounds)
	A	B	C	D	Hp	Phase	Voltage		
VB003	11.83	10.55	10.03	1.25	1/2	3	200-230/460	66	35
VB003S	11.83	10.55	10.03	1.25	1/2	1	115/230	66	42
VB004	12.42	11.88	10.97	1.25	3/4	3	200-230/460	63	40
VB004S	12.42	11.88	10.97	1.25	3/4	1	115/208-230	63	45
VB007	14.75	13.28	12.43	1.50	1 1/2	3	200-230/460	64	60
VB007S	14.75	13.28	12.43	1.50	1 1/2	1	115/208-230	70	65
VB019	15.81	15.36	14.62	1.50	2 1/2	3	200-230/460	73	85
VB019S	15.81	15.36	14.62	1.50	2 1/2	1	115/208-230	70	100
VB030	17.40	16.63	15.55	2.00	4	3	200-230/460	73	130
VB030S	17.40	16.63	15.55	2.00	4	1	115/208-230	71	135
VB037	17.75	17.85	16.69	2.00	5	3	200-230/460	76	150
VB037S	17.75	17.85	16.69	2.00	5	1	115/208-230	74	165
VB055	20.46	20.39	18.74	2.50	7 1/2	3	200-230/460	82	245
VB075	21.50	21.16	20.28	3.00	10	3	200-230/460	81	260
VB110	25.50	23.90	22.24	3.00	15	3	200-230/460	80	370

**Please Note:** All models available in 575 volt, phase 3, and explosion proof | Contact Howden for 50 Hz performance information.

**For further information get in touch with our team today:**

Howden 600 Day Hill Road, Windsor, CT USA 06095

E: [inquiries.usa@howden.com](mailto:inquiries.usa@howden.com) | T: 800 232 4321 | [www.howden.com](http://www.howden.com)