



CX SERIES

AXIAL FANS



Developed to meet the most stringent noise limitations, the COFIMCO **CX series** fan, developed and produced together with [Hudson in USA](#), represents the best in the new generation of **super low noise** fans.

Compared to other fans, the CX series fan allows up to **20 dB(A) noise reduction**, while maintaining the same efficiency.

The AX hub construction consists of one steel disk with a connection flange to facilitate installation on the drive shaft. Blades are connected to the hub with extruded aluminium pillow blocks.

Connection to the driving shaft can be provided through either a cylindrical bore or tapered bushing.

Main applications:

- > Air Cooled Heat Exchanger
- > Packaged and field erected wet cooling towers
- > Air cooled steam condensers



OUR CUSTOMERS



WORK WITH US

