




Howden Cooling Fans



Howden, a Chart Industries Company has a long history of supplying cooling fans going back multiple decades and **totalling more than 100,000 cooling fans.**

Our fibreglass reinforced polyester (FRP) bladed cooling fans are used in industrial cooling systems supplied mainly to the power generation, gas transmission, (petro)chemical and HVAC industries.

Projects summary

>50,000 PCOG

>30,000 Power

>20,000 HVAC

Europe >70.000 CF

Russia >5.000 CF

North America >10.000 CF

Asia-Pacific >10.000 CF

South Africa >2.000 CF

South America >2.000 CF

Australia >1.000 CF



References summary

PCOG

Client	Country	Application	Type	Quantity
Marina South Project	Malaysia	CT	16SX4	10
Shell Godorf	Germany	ACHE	3120SX4	14
DCP1	Saudi Arabia	CT	22SX4	12
Muenster Hafen	Germany	ACHE	16ELFA8	8
Xilinhaote 2	Mongolia	ACC	10ELFA4	60
NAM GLT	Netherlands	ACHE	12SX4	24
Suedzucker Bioethanol Zeitz	Germany	ACHE	16SX3	40
Sluiskil	Netherlands	CT	32ENF7	6
BASF YPC IPS	China	CT	30ENF6	20
Catoosa Gas Station	USA	ACHE	11SX3	15

Power

Client	Country	Application	Type	Quantity
India Cement	India	ACC	36DNF6	10
PP10	Saudi Arabia	ACC	36DNF8	205
TVA Browns Ferry	USA	ACC	10000DNF8	105
POSCO	South Korea	ACC	34DNF7	21
Moorburg Hybrid KT Kraftwerk	Germany	CT	28DVH7	36
Perqueria	Mexico	ACC	28DNF8	14
Petro Amur 2	Indonesia	ACC	36DNM11	6
BISKRA	Algeria	ACC	36DNF8	85
HVC Dordrecht	Netherlands	ACC	34DVF8	6
Datong Yunfent	China	ACC	8910DLF6	30

HVAC

Client	Country	Application	Type	Quantity
Baltimore	Worldwide	CT	FPX	5,000
Guntner	Europe	ACHE	FPX	1,000
Liebherr	Worldwide	ACHE	FPX	2,000
Fincoil	Worldwide	ACHE	FPX	1,500

For further information get in touch with our team today:

cooling.fans@howden.nl | www.howden.cloud/coolingfans

