



Howden Motion



Howden
A Chart Industries Company

Howden Motion

Discover Peak screw compressor performance, efficiency and longevity with Howden Motion



We understand that your compressors are the heart of your operations and using the right oil is paramount to ensure peak performance.

Why Choose Howden Motion Oil?

- Engineered for Excellence**
 Howden Motion is formulated by applications experts to meet OEM standards and align to our compressors' specific requirements. This means your compressors will run smoother
- Unmatched Lubrication**
 Our specially crafted oil provides superior lubrication, minimising wear and tear on vital components, extending service intervals and reducing the risk of costly repairs
- Optimal Thermal Stability**
 Our oil is designed to handle extreme temperatures, maintaining its integrity even under the harshest conditions. Say goodbye to overheating worries and hello to consistent performance
- Enhanced Efficiency**
 By using Howden Motion, you are ensuring that your compressors operate at their highest potential. This leads to energy savings, lower operating costs, and a greener footprint
- Trusted OEM Performance**
 Our oil is the top choice for industry professionals who demand uncompromised performance. With a globally recognised reputation for engineering excellence, Howden has been trusted by industries worldwide for over 165 years

Howden Motion is available for a wide range of process gas and refrigeration applications.


Find out more or make an enquiry



Ensuring equipment longevity and efficiency

Performing effective maintenance on all parts of your compressor system is critical in ensuring uninterrupted performance. This includes the lubricating oil used for your Howden Compressor.

Maintenance for Lubricating Oil



For technical support contact our team by scanning this QR code.



For a tailored product selection contact our sales team by scanning this QR code.



Howden Motion