

# Benefits of New Rotarex Gen II C-Stic

## OLD ROTO-TEL DESIGN



### Roto-Tel Design

Mechanical float assembly  
Analog gauges for each gas service  
Accuracy +/- 5%  
Not calibratable in the field

## NEW ADVANCED ROTAREX GEN II C-STIC



### Rotarex Gen II C-Stic

Capacitance technology  
Digital display that reads 0-100% Full  
Accuracy +/- 1%  
Field calibratable / simple process  
0.5-4.5V ratiometric output /  
supports telemetry  
IP 57 certified  
New robust design