



YOU ASKED, WE LISTENED!

TUF-LITE IV IS NOW AVAILABLE IN SMALLER 11FT-16FT DIAMETERS

Tuf-Lite IV[®]

with Tuf-Edge[®]

Unsurpassed Efficiency & Lower Noise

- Optimized airfoil utilizing CFD
- Enhanced blade shape with twist, taper and sweep
- Backward sweep significantly reduces noise and vibration

Erosion & Chemical Resistance

- Tuf-Edge[®] ceramic leading-edge protection
- Comes standard with UV-resistant pigmented resin and veil

Tuf-Lite[®] Reliability

- Hybrid composite incorporates carbon fiber and fiberglass for maximized strength:weight ratio
- Rigorous static and dynamic structural testing – that provides market leading reliability of Hudson fans
- Standard Hudson warranty of 36 months

Available in Ultra-High Temp[®] version

- Up to 350°F continuous & 400°F intermittent air temperature limits
- Ideal for induced draft air-coolers and for applications with radiant heat potential



Always use the Hudson High Temp Top Bearing with the UHT Fan.



- Uses Hi-Temp Graphite Seals
- Additional Internal Clearance
- Filled with Dow Molykote[®] DC44 High-Temp Grease



**HIGH QUALITY. DURABLE. RELIABLE.
EFFICIENT. CONTINUOUS INNOVATION.**

