

### INSTALLATION MANUAL



## Adjustable Pitch Fan Assembly 11' through 16' Diameter

### *Hudson Tuf-Lite IV<sup>®</sup> fan blades*

Hudson Tuf-Lite IV<sup>®</sup> Ultra Hi Temp (Burnt Orange) fan blades are of single piece fiberglass reinforced plastic (FRP) construction optimized for performance, reliability, noise, and cost effectiveness. Tuf-Lite IV<sup>®</sup> fan blades are constructed of lightweight, corrosion-resistant, fiberglass reinforced vinyl-ester resin, with materials, thickness, and processes determined from finite element analysis modeling. Tuf-Edge<sup>®</sup> leading edge erosion and UV protection is a standard with this blade.

The individually balanced blades can be replaced independently - matched sets are not required.

## RECOMMENDED TOOLS

- Long T-Handle Allen Wrench Set (3/16" to 3/8")
- Medium Size Flat Head Screw Driver
- Brass Ball Peen Hammer
- Flat Bastard File
- 240 Grit Sand Paper
- Anti-Seize Lubricant
- WD-40
- 12" Crescent Wrench
- Shop Towels
- Exact-A-Pitch® Digital Protractor (P/N 62375)
- 25 ft. Measuring Tape
- Pencil or Marker
- Open/Box End Wrench Set (1/2" - 1-1/2")
- Socket Set for 1/2" Drive (1/2" - 1-1/2")
- Torque Wrench(s) Rated for 0-200 ft-lb

## INSTALLATION PROCEDURES

### ASSEMBLY WITH BUSHING

Clean all mating surfaces between hub, bushing and shaft. All grease and lubricant should be removed, leaving the mating surfaces dry.

If there is no shoulder on shaft to prevent bushing from sliding down shaft, slide spacer/sleeve (not provided) on shaft before bushing or use a thrust retainer (optional equipment) on top of hub. Slide bushing and key onto shaft until flush with end of shaft. The shaft size determines the bushing type (Q2, R2, or S2). Lock bushing on shaft by tightening the set screw in flange with an Allen Wrench. (Note: Q2 bushings have no set screws.) Line up key and set hub on bushing. Engage the three (3) cap screws in flange of bushing into hub spool, using a torque wrench with a socket, and tighten evenly. Use the following table to determine the proper tools and torque values.

| Bushing Size | Allen Wrench Size | Cap Screw Size | Socket Size | Torque (ft-lb) Dry |
|--------------|-------------------|----------------|-------------|--------------------|
| Q2           | -                 | 3/8"           | 9/16"       | 29                 |
| R2           | 3/16"             | 3/8"           | 9/16"       | 29                 |
| S2           | 3/16"             | 1/2"           | 3/4"        | 70                 |

### ASSEMBLY WITH TAPERED SHAFT (NO BUSHING REQUIRED)

Clean all mating surfaces between the hub and shaft. Coat all mating surfaces with an anti-seize or lubricating compound.

Align keyways and install hub. Install retainer plate and cap screw(s) with lock washer(s). Shaft size determines what size cap screw is necessary. Using a torque wrench with a socket, evenly tighten cap screw to recommended standard per table below.

| Cap Screw Size | Socket Size | Torque Value (ft-lb) |     |
|----------------|-------------|----------------------|-----|
|                |             | Lubricated           | Dry |
| 5/8" NC        | 15/16"      | 80                   | 90  |
| 3/4" NC        | 1-1/8"      | 120                  | 130 |
| 1" NC          | 1-1/2"      | 150                  | 160 |

NOTE: Retaining arrangement varies with gear shaft design.

### ASSEMBLY WITH STRAIGHT SHAFT (NO BUSHING)

Clean all mating surfaces between the hub and the shaft. If there is no shoulder on shaft to prevent hub from sliding down shaft, slide spacer/sleeve (not provided) on shaft before hub or use a thrust retainer (optional equipment) on top of hub. Install key in shaft. Line up key and keyway and set hub on shaft. Tighten set screw(s) in hub.

#### THRUST RETAINER (optional equipment)

Install proper load bolt (not provided) into top of fan shaft and tighten (See Figure A). Install thrust retainer channel on top hub plate using existing hub spool cap screws. Torque cap screws to 60-65 ft-lb. Install thrust retainer eyebolt and jam nut. Hand tighten eyebolt. Tighten jam nut securely against top of thrust retainer channel.




Figure A

## SEAL DISC HARDWARE INSTALLATION

\*Seal disc mounting hardware must be installed BEFORE installing blades and blade clamps, due to limited working space.

For 4 to 9 Blades:

Install seal disc spacer as shown in Figures 1 and 2. Install 3/8" bolts on the top hub plate with the threaded portion pointing upwards. Place spacer on bolt, then flat washer, and then tighten 3/8" NC nut to recommended standard of 15 ft-lb (lubricated) or 20 ft-lb (dry).




Figure 1




Figure 2

For 10 to 12 Blades:

Install 3/8" NC bolts at six (6) places on top hub plate as shown in Figure 3. Threaded portion of bolts must be pointing up to mount seal disc. Install nut on each bolt. Tighten 3/8" NC nuts to 15 ft-lb (lubricated) and 20 ft-lb (dry).




Figure 3

## BLADE INSTALLATION

To prevent installation problems, work on one blade at a time. Remove blade clamp bolts, nuts, lock washers, and blade clamp halves from hub. Discard the plastic shipping spacers between the upper and lower blade clamp halves. Assemble blade clamp halves over groove in blade neck, and install into hub (See Figure 4). The thick leading edge will be to your left and thin trailing edge will be to your right as you stand at end of blade.




Figure 4

Install clamp bolts through hub plates and blade clamp, putting bolt heads and three belleville spring washers on bottom, and lock nuts on top (See Figure 5). Tighten lightly.

NOTE: Three belleville spring washers should be cupped upward and stacked in the same direction as shown on Figure 5A.




Figure 5




Figure 5A

## SET PITCH AND TRACK

Use Hudson's EXACT-A-PITCH® digital protractor (See Figure 6) or a bubble protractor to set blade pitch. Mount protractor on a flat bar as a base and place it approximately 1" from tip of blade. Note pitch on protractor. Rotate fan 360°, noting high and low pitch readings. Locate place where pitch reading is at mid-point between high and low readings, and set pitch at that point.




Figure 6

Rotate blade in clamp until digital protractor shows specified pitch angle to within  $\pm 0.2^\circ$ . *Fan pitch angle is shown on fan specification sheet for design duty.* After desired pitch angle is set, raise and lower end of fan blade and find mid-point of blade travel. Hold blade at the mid-point. Pull blade outward so that the blade neck flange rests against the back of the blade clamps. Push blade to the right to remove all slack.

Use torque wrench to tighten clamp bolts to 150 ft-lb (lubricated) or 200 ft-lb (dry). Re-check pitch setting. Blade must be set within  $\pm 0.2^\circ$  of desired pitch angle. Tighten clamp bolts evenly. **DO NOT OVER-TORQUE CLAMP BOLTS.**

When bolts are tightened, hold a pencil against top end of blade and mark the level onto a fixed object, such as a pole or the fan ring.

Install remaining blades at same place as first blade, following the instructions above. After tightening bolts, mark top end of each blade in same place first blade was marked. If marks differ by more than  $3/4"$ , adjust blade.

## CHECK TRACK

After fan is installed in fan stack cylinder ring, outline top side of each blade onto fan stack cylinder ring with a marker (See Figure 7). The difference between levels of highest and lowest outlines should be within  $\pm 1"$  if the fan diameter is 11ft - 15ft and within  $\pm 1.5"$  if the fan diameter is 16ft. Correct blade track by loosening clamp bolts and adjusting blade to match track of other blades. Re-tighten bolts and re-check track and pitch angle setting. Re-tighten blade clamp bolts to recommended standard of 120 ft-lb (lubricated) or 130 ft-lb (dry) torque.




Figure 7

## CHECK SWEEP

Measure the distance from trailing edge at blade tip of one blade to trailing edge at blade tip of the adjacent blade (See Figure 7A). This distance should be within  $3/4"$  of each other for all successive blades. Correct blade sweep by loosening clamp bolts and adjusting blade to match sweep of other blades. Re-tighten bolts and re-check sweep and pitch angle setting. Re-tighten blade clamp bolts to recommended standard of 150 ft-lb (lubricated) or 200 ft-lb (dry) torque.




Figure 7A

## SEAL DISC INSTALLATION

For all blade counts:

After installing blades, seal disc should be installed on the previously installed seal disc hardware as shown in Figure 8 for 4 to 9 bladed hubs, or Figure 9 for 10 to 12 bladed hubs. Install flat washer, then place seal disc on top. Install another flat washer, lock washer, and nut on top. Tighten 3/8" NC nut to recommended standard of 15 ft-lb (lubricated) or 20 ft-lb (dry). If difficulty is encountered, loosen bolts on seal flanges until seal disc can be mounted, then re-tighten.




Figure 8 (4 to 9 bladed hub)




Figure 9 (10 to 12 bladed hub)

**NOTE:** The purpose of the seal disc is to prevent hot air from recirculating back down through the hub, increasing efficiency.

## CHECKING TIP CLEARANCE

Rotate fan in position inside fan ring or fan stack to check tip clearance (See Figure 10). The recommended tip clearance is between 3/8" and 3/4". Check for spots where fan blade clearance is not within the recommended tolerance.




Figure 10

If necessary adjust fan ring or fan stack by shimming to obtain proper clearance. For heat exchangers, spacers may be added at the fan ring joints to increase clearance (See Figure 11). Use a chisel to maintain the correct gap until the bolts on the ring are re-tightened.




Figure 11

If a small adjustment is needed, tighten or loosen nut on fan strut in section requiring adjustment (See Figure 12).



Figure 12

## OPERATING INSTRUCTIONS

Start fan and check rotation. Viewed from top (discharge), fan blades should rotate clockwise.

Hudson recommends to re-verify the blade clamp torque after the initial 10-15 minutes of cold operation (i.e., the fan doesn't need to be exposed to the working temperature of the process). This will ensure that the blades are settled within the clamps after the centrifugal forces have acted.

Check motor power consumption to be sure fan is pulling desired load. *CAUTION: If positive pitch is set in summer to use all available motor amps (nameplate rating), motor could be overloaded in winter.* Design pitch angles usually do not use all of the available motor horsepower. This ensures that the motors will not be overloaded at low winter temperatures.

For the fans that have remained idle (such as a shut-down or turn-around), it is highly recommended to re-verify the torque on the blade clamps before putting it back into operation.

For high temperature fan applications, it is recommended to utilize upper fan bearings (See Figure 13) that are rated for high temperature exposure. Hudson can supply a high temperature bearing (Part No. 50081HT) for these specific applications.



Figure 13

## OPERATIONAL LIMITS

Temperature: -100°F to 350°F Continuous,  
400°F Intermittent


Wind speed: 75mph, shut down fan if forecast is higher

**PART LIST**  
**HUDSON PRODUCTS CORPORATION**  
Adjustable Pitch Fan Assembly 11' Thru 16' Diameter  
4000MUHT Series

|      |                                                                                                                            |                 |                              | NO. OF BLADES         |                       |                       |                       |                       |                       |                       |                       |                       |
|------|----------------------------------------------------------------------------------------------------------------------------|-----------------|------------------------------|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|-----------------------|
| ITEM | DESCRIPTION                                                                                                                | TYPE            | PART NO.                     | 4                     | 5                     | 6                     | 7                     | 8                     | 9                     | 10                    | 11                    | 12                    |
|      | 1" Diameter Thru 2.62" Diameter Shaft                                                                                      | Q-2             | Hub Assy. No.<br>Part No.    | 4104KWUHT<br>77443UHT | 4105KWUHT<br>77444UHT | 4106KWUHT<br>77445UHT | 4107KWUHT<br>77446UHT | 4108KWUHT<br>77447UHT | 4109KWUHT<br>77448UHT | 4110KWUHT<br>77449UHT | 4111KWUHT<br>77450UHT | 4112KWUHT<br>77451UHT |
|      | 2.68" Diameter Thru 3.62" Diameter Shaft                                                                                   | R-2             | Hub Assy. No.<br>Part No.    | 4204KWUHT<br>77453UHT | 4205KWUHT<br>77454UHT | 4206KWUHT<br>77455UHT | 4207KWUHT<br>77456UHT | 4208KWUHT<br>77457UHT | 4209KWUHT<br>77458UHT | 4210KWUHT<br>77459UHT | 4211KWUHT<br>77460UHT | 4212KWUHT<br>77461UHT |
|      | 3.68" Diameter Thru 4.19" Diameter Shaft                                                                                   | S-2             | Hub Assy. No.<br>Part No.    | 4304KWUHT<br>77463UHT | 4305KWUHT<br>77464UHT | 4306KWUHT<br>77465UHT | 4307KWUHT<br>77466UHT | 4308KWUHT<br>77467UHT | 4309KWUHT<br>77468UHT | 4310KWUHT<br>77469UHT | 4311KWUHT<br>77470UHT | 4312KWUHT<br>77471UHT |
| 1    | Hub Plate (2 Per Hub)                                                                                                      | Q-2 / R-2 / S-2 | Part No.                     | D5124                 | D4125                 | D4126                 | D4127                 | D4128                 | D4129                 | D4130                 | D4131                 | D4132                 |
| ITEM | DESCRIPTION                                                                                                                | TYPE            | PART NO.                     | QUANTITY PER ASSEMBLY |                       |                       |                       |                       |                       |                       |                       |                       |
| 2    | Hub Spool                                                                                                                  | Q-2             | 65045                        | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     |
|      |                                                                                                                            | R-2             | 65050                        |                       |                       |                       |                       |                       |                       |                       |                       |                       |
|      |                                                                                                                            | S-2             | 65055                        |                       |                       |                       |                       |                       |                       |                       |                       |                       |
| 3    | Bushing                                                                                                                    | Q-2             | Specify<br>Bore              | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     |
|      |                                                                                                                            | R-2             |                              |                       |                       |                       |                       |                       |                       |                       |                       |                       |
|      |                                                                                                                            | S-2             |                              |                       |                       |                       |                       |                       |                       |                       |                       |                       |
| 4    | Blade Clamp Half, Un-painted Aluminum (Standard)<br>Option 1: Epoxy coated Aluminum<br>Option 2: Epoxy coated Ductile Iron |                 | 4742A<br><br>C4742A<br>65010 | 8                     | 10                    | 12                    | 14                    | 16                    | 18                    | 20                    | 22                    | 24                    |
| 5    | Blade Clamp Bolt With Nut 3/4"-10 x 10" (Mech. Galv.)                                                                      |                 | 79299                        | 8                     | 10                    | 12                    | 14                    | 16                    | 18                    | 20                    | 22                    | 24                    |
| 6    | Belleville Spring Washer, SS                                                                                               |                 | 82737                        | 24                    | 30                    | 36                    | 42                    | 48                    | 54                    | 60                    | 66                    | 72                    |
| 7    | 3/4" Hex Steel Top Lock Nut, Grade C (Zinc Finish)                                                                         |                 | 82736                        | 8                     | 10                    | 12                    | 14                    | 16                    | 18                    | 20                    | 22                    | 24                    |
| 8    | Stop Plate Sub-Assembly                                                                                                    | Q-2 / R-2 / S-2 | B4113                        | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     |
| 9    | Stop Plate Bolt 3/4"-10 x 5" (Zinc Plated)                                                                                 |                 | 51709                        | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     |
| 10   | 3/4" Lock washer (Mech. Galv.)                                                                                             |                 | 73738                        | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     |
| 11   | 3/4" Flat Washer (Mech. Galv.)                                                                                             |                 | 73640                        | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     |
| 12   | Hub Spool Bolt 5/8"-11 x 1 1/2" (316 SS)                                                                                   |                 | 72402                        | 16                    | 16                    | 16                    | 16                    | 16                    | 16                    | 16                    | 16                    | 16                    |
| 13   | 5/8" Lock washer (316 SS)                                                                                                  |                 | 73731                        | 16                    | 16                    | 16                    | 16                    | 16                    | 16                    | 16                    | 16                    | 16                    |
| 14   | 42" Dia. Seal Disc (3-6 blades)                                                                                            |                 | 81110HT                      | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     | 1                     |
|      | 53" Dia. Seal Disc (7-9 blades)                                                                                            |                 | 81114HT                      |                       |                       |                       |                       |                       |                       |                       |                       |                       |
|      | 64" Dia. Seal Disc Kit* (10-12 Blades)                                                                                     |                 | 81115HT                      |                       |                       |                       |                       |                       |                       |                       |                       |                       |
| 15   | Seal Disc Spacer 4" height                                                                                                 |                 | B4328                        | 4                     | 5                     | 6                     | 6                     | 6                     | 6                     | 0                     | 0                     | 0                     |
|      | Spacer Bolt, HH, 3/8"-16 x 5 1/2 (316 SS)                                                                                  |                 | 78659                        | 4                     | 5                     | 6                     | 6                     | 6                     | 6                     | 0                     | 0                     | 0                     |
|      | 3/8" Hex Nut (316 SS)                                                                                                      |                 | 72050                        | 8                     | 10                    | 12                    | 12                    | 12                    | 12                    | 0                     | 0                     | 0                     |
|      | 3/8" Flat Washer (316 SS)                                                                                                  |                 | 73623                        | 12                    | 15                    | 18                    | 18                    | 18                    | 18                    | 0                     | 0                     | 0                     |
|      | 3/8" Lock washer (316 SS)                                                                                                  |                 | 73722                        | 4                     | 5                     | 6                     | 6                     | 6                     | 6                     | 0                     | 0                     | 0                     |
|      | Seal Disc Bolt 3/8"-16 X 1 1/2" (316 SS)                                                                                   |                 | 60274                        | 0                     | 0                     | 0                     | 0                     | 0                     | 0                     | 6                     | 6                     | 6                     |
|      | 3/8" Flat Washer (316 SS)                                                                                                  |                 | 73623                        | 0                     | 0                     | 0                     | 0                     | 0                     | 0                     | 12                    | 12                    | 12                    |
|      | 3/8" Lock washer (316 SS)                                                                                                  |                 | 73722                        | 0                     | 0                     | 0                     | 0                     | 0                     | 0                     | 6                     | 6                     | 6                     |
|      | 3/8" Hex Nut (316 SS)                                                                                                      |                 | 72050                        | 0                     | 0                     | 0                     | 0                     | 0                     | 0                     | 12                    | 12                    | 12                    |
| 16   | Tuf-Lite IV® Ultra Hi Temp Fan Blade (Burnt Orange)                                                                        |                 | (Varies)                     | 4                     | 5                     | 6                     | 7                     | 8                     | 9                     | 10                    | 11                    | 12                    |

# HUDSON PRODUCTS CORPORATION

## Adjustable Pitch Fan Assembly 11' Thru 16' Diameter Series 4000MUHT



### STANDARD MATERIALS & FINISHES

**Blades:** Fiberglass reinforced vinyl-ester or epoxy  
**Hub Spool:** Ductile Iron, Zinc Rich Coating  
**Plates:** Steel, Galvanized  
**Bushing:** Malleable Iron  
**Seal Disc:** Fiberglass Reinforced Polyester

**Blade Clamps:**  
 Un-painted Aluminum (Standard)  
 Epoxy Coated Aluminum (Option 1)  
 Epoxy Coated Ductile Iron (Option 2)  
**Fasteners:**  
 Steel, Mech. Galvanized & 316 SS Opt.  
 Complete Fan W/316 SS (Option 1)  
 Complete Fan W/K500 Monel (Option 2)

**WHEN ORDERING, SPECIFY FAN DIAMETER, TYPE & NUMBER OF BLADES & SHAFT DIAMETER**

EXAMPLE:

APT

16MUHT

6

2 7/8" BORE

Fan Model  
Adjustable Pitch

Fan Diameter & Blade Type  
(Specify "MUHT" for Tuf-Lite IV® Ultra Hi Temp Blades)

Number  
of Blades

Shaft Diameter

# **HUDSON**

## **Products Corporation**

9660 Grunwald Rd.  
Beasley, Texas 77417-8600  
Phone: 281-396-8100  
Fax: 281-396-8388  
1-800-634-9160 (24 Hours)  
[EMAIL: Tuf-liteorders@hudsonproducts.com](mailto:Tuf-liteorders@hudsonproducts.com)  
<http://www.hudsonproducts.com>

Hudson, Auto-Variable, Combin-Aire, Exact-A-Pitch, Fin-Fan, Heatflo, Hy-Fin, Split-Flo, Solo Aire, Stac-Flo, Steamflo, Thermflo, Tuf-Edge, Tuf-Lite, Tuf-Lite II, Tuf-Lite III and Tuf-Lite IV are registered trademarks of Hudson Products Corporation.

©2024 Hudson Products Corp. All Rights Reserved.