


# ON THE LEADING EDGE OF AXIAL FAN DESIGN

## Tuf-Lite III<sup>®</sup> with Tuf-Edge<sup>®</sup>

- Chart's one-piece FRP aerodynamic blade
- Most efficient blade in industry
- Highest quality and reliability
- Individually balanced and interchangeable
- Fatigue resistant vinyl-ester resin with Tuf-Edge<sup>®</sup> ceramic leading edge erosion protection
- Ultraviolet resistant
- Erosion and chemical resistant
- High temperature and static capabilities
- Sizes range from 6 ft to 33 ft in diameter
- Manufactured in the United States
- Fastest delivery in the market
- Unsurpassed customer service



Always use the Hudson High Temp Top Bearing with the UHT Fan.



- Uses Hi-Temp Graphite Seals
- Additional Internal Clearance
- Filled with Dow Molykote<sup>®</sup> DC44 High-Temp Grease



**HIGH QUALITY. DURABLE. RELIABLE.  
EFFICIENT. CONTINUOUS INNOVATION.**

