

Bearing Down On The Competition?



You bet.

The NEW Self-Aligning Shaft Bearings from HUDSON PRODUCTS CORPORATION are engineered to provide 80% higher thrust capacity and extended bearing life. Major field mounting expenses are also eliminated when coupled with Hudson's updated Bearing Adapter units.



Features include:

- 200% increased lifespan over previous designs
- 80% Higher thrust capacity than type "E" or "K" bearings
- Self-aligning
(can compensate for ± 1 degree misalignment)
- Prevents water accumulation with cast-in water channels and special seal arrangement
- Easily adaptable to existing air-cooled heat exchangers without the need for welding, drilling, or hot work permits

For more information on this or any other product, please contact:

HUDSON PRODUCTS CORPORATION

9660 Grunwald Road, Beasley, Texas 77417-8600

Phone: (281) 396-8100

Fax: (281) 396-8211

1-800-634-9160 (24 Hours)

E-Mail: HUDSONPRODUCTS@HUDSONPRODUCTS.COM



A Subsidiary of Hudson Products Holdings, Inc.

Copyright © Hudson Products Corporation


www.hudsonproducts.com

Bearing Specifications

*Top Expansion Radial Bearing 50081


- 2-15/16" bore
- Self-aligning ball bearing
- *Basic "C" rating = 11,600lb
- *Static "Co" rating = 9,620lb
- ± 1 degree misalignment allowed
- 6" x 6" mounting holes 13/16" bore
- Uses felt contact seals (special orientation)
- Temperature range: -20°F to 275°F (-29°C to 135°C)
- Single locking collar with dog point set screw pre-assembled
- Collar-mounted flinger installed
- Weight: 18lbs

* In normal cases, this bearing sees no thrust loads, only radial loads.



Bottom Thrust Bearing 50080

- 2-15/16" bore
- Self-aligning spherical roller bearing
- Basic "C" rating = 51,000lb
- Static "Co" rating = 90,700lb
- ± 1 degree misalignment allowed
- 7" x 7" mounting holes 13/16" diameter
- 6" x 6" pattern also available. (P/N: 50082)
- Temperature range: -20°F to 275°F (-29°C to 135°C)
- Adapts to 6" x 6" mounting holes with adapter plate
- Will fit existing Hudson Products Corporation units with 10' or larger fans
- Custom designed housing with drain grooves for "inverted" installation
- Two locking collars
- Weight: 46lbs



NEW Bearing Adapter Unit

Features include:

- No cutting or burning required
- All necessary hardware is included
- Converts 6" x 6" hole patterns to accommodate a 7" x 7" pattern
- Bearing installations are more predictable and reliable
- Weighs only 14lbs.

Two models of the newly available bottom bearing adapters are designed to fit Hudson Air-Cooled Heat Exchangers only.



A Subsidiary of Hudson Products Holdings, Inc.
Copyright © Hudson Products Corporation

HUDSON Products Corporation continues to be a major force in the Air-Cooled Heat Exchanger industry. And with the introduction of a new line of bearings and adapter unit, our competitors will be playing catch up for a long time.